



Silkscreened plain mounting plate H400xW300mm made of galvanised sheet steel

Local distributor code: 392865649

NSYMS43

! Discontinued on: 7 Aug 2023

! Discontinued

EAN Code: 3606480183782

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- H: 400 mm W: 300 mm - H: 300 mm W: 400 mm	
Mounting Location	Direct fixing on backstuds Step slide	
Mounting Plate Description	Plain	
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	Set Set of 1	
Material	Galvanised steel	
Surface Finish	Silkscreened	

Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element	
Permanent Permissible Load	60 kg	
Height	250 mm	
Width	350 mm	
Depth	125 mm	
Thickness	2 mm	
Net Weight	1.377 kg	
Variant Particularity	Centimetric grid pattern	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.3 cm
Package 1 Width	25.5 cm
Package 1 Length	35 cm

Package 1 Weight	1.278 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	280
Package 2 Height	42 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	371 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations