Product datasheet

Specifications

, Green Premium[™]



Silkscreened plain mounting plate H500xW400mm made of galvanised sheet steel

Local distributor code: 392865678

NSYMS54

() Discontinued on: 11 Aug 2023

(!) Discontinued

EAN Code: 3606480183829

	•
M	ain
	G 111

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 500 mm W: 400 mm
Mounting Location	Step slide Direct fixing on backstuds
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	Galvanised steel
Surface Finish	Silkscreened

Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element
Permanent Permissible Load	90 kg
Height	450 mm
Width	350 mm
Depth	125 mm
Thickness	2 mm
Net Weight	2.494 kg
Variant Particularity	Centimetric grid pattern

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.2 cm
Package 1 Width	35 cm
Package 1 Length	45 cm

Package 1 Weight	2.334 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	140
Package 2 Height	37 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	340 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations