

Product datasheet

Specifications



DLP modular dist chassis 264modules(18mm) insulating material for PLA H1500xW750

Local distributor code:
403418930

NSYDLP264G

EAN Code: 3606485422848

Main

Range	Thalassa
Accessory / Separate Part Category	Mounting accessory
Application	Multi-purpose Modular distribution application
Product Or Component Type	Chassis
Device Short Name	DLP
For Enclosure Nominal Dimensions	-
Mounting Location	Front of enclosure
Range Compatibility	Thalassa Thalassa PLA Thalassa Thalassa PHD
Device Composition	1 chassis structure 1 neutral/earth strip 2 x 16 mm ² 5 x 6 mm ² 1 plain front panel 8 front panels with 35 mm DIN rail
Additional Information	IP2x not respected when chassis is mounted at 67 mm

Complementary

Material	Front panel: self-extinguishing Chassis structure and rails: galvanised steel
Colour	Front panel: grey (RAL 7035)
Fixing Mode	By fixing element - on front with supports location
Adjustment	In height from 40 to 85 mm for DIN rail
Number Of Horizontal Rows	8
Total Number Of 18 Mm Modules	264
Type Of Front Plate	Plain and cut-out plates
Number Of Cut-Out	8 cut-outs
Height	1500 mm
Width	750 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.0 cm
Package 1 Width	68.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	143.5 cm
Package 1 Weight	6.6 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations