# **Product datasheet**

Specifications





# Microperforated mounting plate H300xW200 w/holes diam 3,6mm on 12,5mm pitch

Local distributor code: 385511832 NSYMF32

EAN Code: 3606480199066

#### Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
<b>Enclosure Nominal Dimensions</b>	- H: 300 mm W: 200 mm
Mounting Location	Direct fixing on backstuds Step slide
Mounting Plate Description	Microperforated
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	Galvanised steel

### Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element
Permanent Permissible Load	60 kg
Height	265 mm
Width	150 mm
Depth	125 mm
Thickness	1.8 mm
Net Weight	0.56 kg

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.5 cm
Package 1 Width	15 cm
Package 1 Length	27 cm
Package 1 Weight	560 g
Unit Type Of Package 2	P12
Number Of Units In Package 2	250

Package 2 Height	43 cm	
Package 2 Width	80 cm	
Package 2 Length	120 cm	
Package 2 Weight	160 ka	

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>②</b>	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	