Product datasheet

Specifications



Monobloc perforated plates H1400xW1000mm with universal perforations 11x26mm

Local distributor code: 398249421

NSYMR1410

EAN Code: 3606480310683

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 1400 mm W: 1000 mm
Mounting Location	Step slide Direct fixing on backstuds
Mounting Plate Description	Telequick perforated
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	Steel
Surface Finish	Zinc coated

Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element
Height	1345 mm
Width	951 mm
Depth	15 mm
Thickness	2 mm
Net Weight	8.626 kg
Number Of Slots	2728
Variant Particularity	Installation in rear of enclosure
Cut-Out Dimensions	11 x 26 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	95 cm
Package 1 Length	134.5 cm

Package 1 Weight	9 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	35
Package 2 Height	90 cm
Package 2 Width	220 cm
Package 2 Length	80 cm
Package 2 Weight	380 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations