# **Product datasheet**

Specifications





# Monobloc perforated plates , H400xW300mm with universal perforations 11x26mm

Local distributor code: 392865432

NSYMR43

EAN Code: 3606480183645

#### Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 400 mm W: 300 mm
Mounting Location	Direct fixing on backstuds Step slide
Mounting Plate Description	Telequick perforated
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	Steel
Surface Finish	Zinc coated

#### Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element	
Height	348 mm	
Width	251 mm	
Depth	15 mm	
Thickness	2 mm	
Net Weight	0.682 kg	
Number Of Slots	198	
Variant Particularity	Installation in rear of enclosure	
Cut-Out Dimensions	11 x 26 mm	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	25.0 cm
Package 1 Length	35.0 cm

Package 1 Weight	720.0 g
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	572
Package 2 Height	90.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	434.0 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations