



Silkscreened plain mounting plate H600xW600mm made of galvanised sheet steel

Local distributor code: 392865694 NSYMS66

! Discontinued on: 9 Oct 2023

! Discontinued

EAN Code: 3606480183843

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- H: 600 mm W: 600 mm	
Mounting Location	Step slide Direct fixing on backstuds	
Mounting Plate Description	Plain	
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	y Per Set Set of 1	
Material	Galvanised steel	
Surface Finish	Silkscreened	

Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element	
Permanent Permissible Load	135 kg	
Height	550 mm	
Width	550 mm	
Depth	125 mm	
Thickness	2 mm	
Net Weight	4.808 kg	
Variant Particularity	Centimetric grid pattern	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.3 cm
Package 1 Width	55 cm
Package 1 Length	56.5 cm

Package 1 Weight	4.298 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	70
Package 2 Height	34 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	314 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations