



Internal door for Spacial WM encl. H500xW400 steel, RAL7035.Adjustable in depth

Local distributor code:
392869959
NSYPIN54

EAN Code: 3606480168567

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Step slide Front side
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3X
Device Composition	1 door 4 fixing brackets 2 mounting uprights

Complementary

Material	Door: sheet steel
Colour	All faces: grey (RAL 7035)
Surface Finish	Polyester powder
Lock Type	Lock 3 mm double bar
Number Of Locks	1
Adjustment	Pitch 25 mm (on step slides)
Door Type	Internal plain
Door Opening Side	Reversible
Maximum Load	30 kg/m²
Height	Nominal: 500 mm
Width	Nominal: 400 mm
Net Weight	2.8 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	36.000 cm
Package 1 Length	47.000 cm

Package 1 Weight	2.561 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	5
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	13.455 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	40
Package 3 Height	90.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	119.640 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations