

Product datasheet

Specifications



Metal industrial box hinges transparent cover H200xW600xD120 IP55 IK08 RAL 7035

NSYSBMB206012

! Discontinued

! Discontinued on: 5 Dec 2020

EAN Code: 3606480520440

Main

| | |
|--------------------------|------------------------------------------------------------------------------------|
| Range | Spacial |
| Product Name | Spacial SBM |
| Device Application | Multi-purpose |
| Category | Industrial box |
| Device Short Name | SBMB |
| Enclosure Type | Bus box |
| Enclosure Nominal Height | 200 mm |
| Enclosure Nominal Width | 600 mm |
| Enclosure Nominal Depth | 120 mm |
| Enclosure Mounting | Wall mounted |
| Device Composition | 1 body 4 FL21 cable gland plate 1 glazed door 1 DIN rail 3 cover screw |
| Body Type | Single piece body folded and welded |
| Type Of Front Cover | Glazed door |
| Cover Fixing | Half turn metal screw |
| Lock Type | Captive screw PZ2 outside sealed area |
| Removable Parts | Cover by captive screws Cable gland plate screw DIN rail screw |

Complementary

| | |
|------------------------|--------------------------------------------------|
| Material | Cover: steel and plexiglass Body: sheet steel |
| Surface Finish | Polyester powder |
| Colour | Grey (RAL 7035) |
| Standards | IEC 62208 |
| Product Certifications | LR DNV BV UL GL |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|--------------------------------------------|------------------------------|
| Ip Degree Of Protection | IP55 conforming to IEC 60529 |
| Ik Degree Of Protection | IK08 conforming to IEC 62262 |
| Ambient Air Temperature For Storage | -35...60 °C |
| Operating Temperature | -35...80 °C |
| Net Weight | 6.354 kg |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty | 18 months |
|-----------------|-----------|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)