# **Product datasheet**

Specifications





### Spacial S3D 2 plain door w/o mount.plate. H800xW1200xD300.IP55 IK10 RAL7035.

Local distributor code: 392867142

NSYS3D81230D

#### EAN Code: 3606480159022

#### Main

#### Complementary

· · · · · · · · · · · · · · · · · ·	
Body Type	Gutter-shaped front rail double sheet thickness Single piece body
Number Of Doors	Front face: 2 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Steel
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	UL GL DNV cUL LR BV
Net Weight	45 kg

### Environment

Electromagnetic Compatibility	Electromagnetic field immunity test
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP55 conforming to IEC 60529

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	34.5 cm
Package 1 Width	81.5 cm
Package 1 Length	121.5 cm
Package 1 Weight	45 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	95.5 cm
Package 2 Width	80 cm
Package 2 Length	122 cm
Package 2 Weight	101 kg

### **Contractual warranty**

Warranty

18 months

### Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations