Product datasheet

Specification





Spacial SM compact enclosure with mounting plate - 2000x800x600 mm

Local distributor code: 383546993 NSYSM20860P

EAN Code: 3606485120379

Main

Range	Spacial
Product Name	Spacial SM
Product Or Component Type	Compact enclosure
Application	Multi-purpose
Installation Accessory Type	Floor-standing
Device Composition	1 body 1 cable gland plate 1 locking system with handle: door 4 mounting plate bracket 1 mounting plate 1 door
Removable Parts	Door by screws hinge Mounting plate by screws mounting plate bracket Mounting plate bracket by screws
Enclosure Nominal Height	2000 mm
Enclosure Nominal Width	800 mm
Enclosure Nominal Depth	600 mm

Complementary

•	
Number Of Doors	Front: 1 door(s)
Door Opening Side	Reversible (120 °)
Door Type	Plain
Lock Type	4 points lock, handle with 5 mm double bar insert
Body Type	Single piece body with welded rear panel Front part forming a rigid frame with welded corners
Mounting Plate Description	Plain
Type Of Gland Plate	Standard
Cable Entry	1 entry
Material	Mounting plate: galvanised steel Body: sheet steel Door: sheet steel Hinge: zamak
Surface Finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)
Accessibility For Operation	Front
Net Weight	142 kg

Environment

Standards	IEC 62208
Product Certifications	BV UL DNV
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP55 conforming to IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	213.000 cm
Package 1 Width	84.500 cm
Package 1 Length	68.500 cm
Package 1 Weight	144.917 kg

Logistical informations

Country Of Origin

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations