Product datasheet

Specification





SMX 304L stainless monobloc enclosure, H2000xW1600xD600mm, Scotch Brite® finish.

Local distributor code:

383545570 NSYSMX201660

EAN Code: 3606480155888

Main

Range	Spacial
Product Name	Spacial SMX
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	2000 mm
Nominal Width	1600 mm
Nominal Depth	600 mm
Product Installation	Floor-standing
Device Composition	body door cable gland plate locking system with handle: door mounting plate bracket

Complementary

Body Type	Single piece body folded and welded
Door Type	Plain
Door Opening Side	Reversible (120 °)
Number Of Doors	Front face: 2 door(s)
Lock Type	3 points lock, handle with 5 mm double-bar insert
Type Of Gland Plate	Plain
Accessibility For Operation	Front
Mounting Plate Description	Without mounting plate
Material	Body and door: stainless steel 304L Handle: zamak Hinge: stainless steel
Removable Parts	Door by hinges Mounting plate bracket by screws Cable gland plate by clips
Surface Finish	Enclosure: Scotch-Brite® brushed Handle: painted
Net Weight	200 kg

Environment

Standards IEC 62208

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Product Certifications	CAN/CSA 22 UL 508
Environmental Characteristic	Specific hygiene Corrosive

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	68.0 cm
Package 1 Width	165.0 cm
Package 1 Length	213.0 cm
Package 1 Weight	212.0 kg

Logistical informations

Country Of Origin BG

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations