# **Product datasheet**

Specifications





# Spacial SF/SM side panel plinth - 100x600 mm

Local distributor code: 398323635

NSYSPS6100

EAN Code: 3606485126630

#### Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Side plinth
Application	Compartmentalised application PC application Multi-purpose Electronic application Prisma application
Nominal Dimensions Of The Housing	-
Device Composition	fixing elements 4 corner cover 2 side panel
Range Compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFM
Mounting Support	Front plinth

## Complementary

Fixing Mode	By screws
Colour	Grey (RAL 7022)
Surface Finish	Epoxy-polyester powder
Height	100 mm
Width	Nominal: 600 mm

## **Environment**

Ip Degree Of Protection	IP20 (complete plinth)
Ik Degree Of Protection	IK10

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	12.000 cm
Package 1 Length	45.500 cm
Package 1 Weight	1.752 kg
Unit Type Of Package 2	S04

Number Of Units In Package 2	12
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	21.674 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	48
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	98.696 kg

## **Logistical informations**

Country Of Origin F

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations