



Spacial SF/SM universal cross rails - 90 mm

Local distributor code:

1917723

NSYSUCR9050

EAN Code: 3606485133669

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Universal cross rail
Application	Multi-purpose
Nominal Dimensions Of The Housing	- H: 500 mm

Complementary

Range Compatibility	Spacial Spacial SF	
	Spacial Spacial SM	
	Spacial Spacial SFX	
	Spacial Spacial SMX	
Mounting Location	Between cross rails	
Mounting Support	Adaptation profile, on SM enclosures	
Device Composition	fixing elements	
	2 cross rails	
	4 supports	
Quantity Per Set	Set of 1	
Material	Steel	
Surface Finish	Galvanized	
Fixing Mode	By screws	
Adjustment	ent Adjustable with a pitch of 25 mm	
Number Of Horizontal Rows	3	
Maximum Load	120 kg	
Height	Nominal: 500 mm	
•	Useful: 407 mm	
Width	90 mm	
Depth	27 mm	
Thickness	1.5 mm	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	9.5 cm

Package 1 Length	40.5 cm
Package 1 Weight	1.376 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	320
Package 2 Height	100 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	455 kg

Logistical informations

Country Of Origin

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations