Product datasheet

Specification





Spacial SM compact enclosure with mounting plate - 1400x800x400 mm

Local distributor code: 383546744 NSYSM14840P

EAN Code: 3606485120072

Main

Range	Spacial
Product Name	Spacial SM
Product Or Component Type	Compact enclosure
Application	Multi-purpose
Installation Accessory Type	Floor-standing
Device Composition	1 body 1 cable gland plate 1 locking system with handle: door 4 mounting plate bracket 1 mounting plate 1 door
Removable Parts	Door by screws hinge Mounting plate by screws mounting plate bracket Mounting plate bracket by screws
Enclosure Nominal Height	1400 mm
Enclosure Nominal Width	800 mm
Enclosure Nominal Depth	400 mm

Complementary

Number Of Doors	Front: 1 door(s)	
Door Opening Side	Reversible (120 °)	
Door Type	Plain	
Lock Type	4 points lock, handle with 5 mm double bar insert	
Body Type	Single piece body with welded rear panel Front part forming a rigid frame with welded corners	
Mounting Plate Description	Plain	
Type Of Gland Plate	Standard	
Cable Entry	1 entry	
Material	Mounting plate: galvanised steel Body: sheet steel Door: sheet steel Hinge: zamak	
Surface Finish	Epoxy-polyester powder	
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)	
Accessibility For Operation	Front	
Net Weight	80 kg	

Environment

Standards	IEC 62208
Product Certifications	UL DNV BV
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP55 conforming to IEC 60529

Packing Units

· acimig cime	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	153.0 cm
Package 1 Width	84.5 cm
Package 1 Length	49.0 cm
Package 1 Weight	80.0 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	98 cm
Package 2 Width	85 cm
Package 2 Length	153 cm
Package 2 Weight	180 kg

Logistical informations

Country Of Origin

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations