Product datasheet

Specification





TeSys Vario enclosed, emergency stop switch disconnector, 20A, IP55

Local distributor code:

386306761 VCFN25GE

EAN Code: 3389110897708

Main

Range	TeSys	
Product Name	TeSys Mini-VARIO	
Device Short Name	VCFN	
Product Or Component Type	Emergency stop switch disconnector	
Performance Level	Standard	
Poles Description	3P	
Control Type	Rotary handle	
Handle Colour	Red	
Handle Front Plate Colour	Yellow	
Rotary Handle Padlocking	1 to 3 padlocks 48 mm	

Complementary

o op. o o y		
Marking	0 - 1	
[Ue] Rated Operational Voltage	690 V AC	
[Uimp] Rated Impulse Withstand Voltage	8 kV	
[Ithe] Conventional Enclosed Thermal Current	20 A	
[le] Rated Operational Current	14.5 A (AC-23A) at 400 V	
Rated Operational Power In W	7.5 kW at 400 V (AC-23) 5.5 kW at 400 V (AC-3)	
Intermittent Duty Class	30	
Making Capacity (I Rms)	250 A at 400 V AC-21A	
[Icw] Rated Short-Time Withstand Rms Current	150 A at 400 V duration: 1 s	
Rated Conditional Short-Circuit Current	10 kA at 400 V	
Suitability For Isolation	Yes	
Fire Resistance	960 °C conforming to IEC 60595-2-1	
Handle Front Plate Dimension	60 x 60 mm	
Height	131 mm	
Width	82.5 mm	
Depth	106 mm	
Net Weight 0.512 kg		

Environment

Standards	IEC 60947-4-1	
Protective Treatment	TC	
Mechanical Robustness	Vibrations 10150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27	
Ambient Air Temperature For Operation	-2050 °C	

Packing Units

PCE
1
8.500 cm
11.500 cm
13.500 cm
350.000 g
S02
7
15.000 cm
30.000 cm
40.000 cm
2.689 kg
P06
112
75.000 cm
80.000 cm
60.000 cm
51.024 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations