Product datasheet

Specifications





empty control station - light grey base and cover

Local distributor code: 403020412

XALE1

EAN Code: 3389119017572

Main

Range Of Product	Harmony XALE
Product Or Component Type	Empty control station
Device Short Name	XALE
Product Destination	For XB7 Ø 22 mm control and signalling units
Number Of Cut-Out	1 cut-out
Colour Of Base Of Enclosure	Light grey (RAL 7035)
Colour Of Cover	Light grey (RAL 7035)
Material	ABS (acrylonitrile butadiene-styrene)
Cable Entry	2 knock-outs, clamping capacity: 16 mm 4 knock-outs for ISO M20
Sale Per Indivisible Quantity	5
Ip Degree Of Protection	IP54 conforming to IEC 60529

Complementary

Assembly Style	For customer assembly	
Net Weight	0.08 kg	
Marking	CE	

Environment

Protective Treatment	тс
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2555 °C
Electrical Shock Protection Class	Class II conforming to IEC 60536
Ik Degree Of Protection	IK05 conforming to EN 50102
Standards	EN/IEC 62208 EN/IEC 60947-5-1 EN/IEC 60947-5-5 EN/IEC 60947-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.200 cm
Package 1 Width	8.100 cm

11.500 cm
72.000 g
BB1
5
8.300 cm
8.100 cm
31.300 cm
414.000 g
\$03
45
30.000 cm
30.000 cm
40.000 cm
4.200 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Product datasheet

Dimensions Drawings

Dimensions



- (1) 4 ISO 20 knock-outs.
- (2) 2 knock-outs for cable entry, maximum capacity 16 mm / 0.63 in.
- (3) 2 knock-out elongated fixing holes Ø 3 mm x 5 mm / Ø 0.12 in. x 0.20 in.

Control station XALE fitted with:	c in mm	c in in.
Flush pushbutton	61	2.40
Projecting pushbutton	63	2.48
Illuminated pushbutton	66.5	2.62
Pilot light	63	2.48
Emergency stop without key	81.5	3.21
Selector switch with standard handle	76.5	3.01
Key switch	92	3.62