Product datasheet

Specifications





empty flush mounted box - XAP-E - insulated material - without opening - IP 65

Local distributor code: 388805888

XAPE902

EAN Code: 3389110628128

Main

Range Of Product	Harmony XAP		
Product Or Component Type	Protective rear cover		
Device Short Name	XAPE		
Product Destination	For front plate XAPE302		
Material	Insulated material		
Cable Entry	Knock-out cable entries		
Product Mounting	Flush mounting		
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010		
Resistance To Chemical Agents	Good resistant to acetone Good resistant to alcohols Good resistant to chloride and fluoride solvents Good resistant to diluted mineral acids Good resistant to oils and petrol Good resistant to organic acids Good resistant to salts		

Complementary

Net Weight

0.05 kg

Environment

Protective Treatment	тс тн
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2570 °C
Electrical Shock Protection Class	Class I conforming to IEC 60536 Class I conforming to NF C 20-030

Packing Units

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	8.0 cm
Package 1 Length	8.0 cm
Package 1 Weight	60.0 g
Unit Type Of Package 2	S02

Number Of Units In Package 2	18
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.38 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	

Product datasheet

Dimensions Drawings

Dimensions and Mounting



P Usable depth

b		Р	
mm	in.	mm	in.
85	3.35	82.5	3.25

4