


Product datasheet

Specifications



Spacial SF side panel plinth - 100x800 mm

Local distributor code:
398323677

NSYSPS8100

EAN Code: 3606485126647

Overview

Lead Time Usually Ships within 4 Weeks

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Side plinth
Application	Compartmentalised application PC application Prisma application Multi-purpose Electronic application
Nominal Dimensions Of The Housing	-
Device Composition	fixing elements 4 corner cover 2 side panel
Range Compatibility	Spacial Spacial SF Prisma Prisma PH Spacial Spacial SFM
Mounting Support	Front plinth

Complementary

Fixing Mode	By screws
Colour	Grey (RAL 7022)
Surface Finish	Epoxy-polyester powder
Height	100 mm
Width	Nominal: 800 mm

Environment

Ip Degree Of Protection	IP20 (complete plinth)
Ik Degree Of Protection	IK10

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	11.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	66.000 cm
Package 1 Weight	2.963 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	55
Package 2 Height	45.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	174.965 kg

Logistical informations

Country Of Origin	ES
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations