



84mm Rotating Mirror Orange 24VAC-DC

Local distributor code: 398334284

XVR08B05

EAN Code: 3606480033001

Main

Range Of Product	Harmony XVR	
Product Or Component Type	Prewired rotating mirror beacon	
Sound Signalling	Without	
Device Short Name	XVR	
Mounting Diameter	84 mm	
Ip Degree Of Protection	IP65 (with accessory) conforming to IEC 60529 IP23 conforming to IEC 60529	
[Us] Rated Supply Voltage	24 V AC/DC	
Light Source	High luminosity LED, orange	

Complementary

Material	ABS (acrylonitrile butadiene-styrene): body part PC: globe	
Cad Overall Width	84 mm	
Cad Overall Depth	84 mm	
Net Weight	0.3 kg	
Marking	CE	
Product Mounting	By 3 M4 screws	
Supply Voltage Limits	1930 V DC 21.626.4 V AC	
[Uimp] Rated Impulse Withstand Voltage	0.8 kV	
Current Consumption	125 mA	
Flashing Frequency	2.3 Hz	
Clamping Connection Capacity	0.83 mm²	
Awg Gauge	AWG 18	
Cable Length	500 mm	

Environment

Standards	IEC 61000-6-4 IEC 61000-6-2	
Product Certifications	UL	
Protective Treatment	TC	
Ambient Air Temperature For Storage	-3570 °C	

Ambient Air Temperature For Operation	-1050 °C
Electrical Shock Protection Class	Class II conforming to IEC 61140

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.5 cm
Package 1 Width	10.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	393.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.051 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information


XVR08B05

Dimensions Drawings

Rotating Mirror Beacon

Dimensions





Product datasheet

XVR08B05

Mounting and Clearance

Rotating Mirror Beacon

Panel Cut-out

