



# 84mm Rotating Mirror Green 12VAC-DC

XVR08J03

① Discontinued on: 31 Mar 2022

! End-of-service on: 17 Oct 2020

(!) Discontinued

EAN Code: 3606480032974

# Main

Range Of Product	Harmony XVR	
Product Or Component Type	Prewired rotating mirror beacon	
Sound Signalling	Without	
Device Short Name	XVR	
Mounting Diameter	84 mm	
Ip Degree Of Protection	IP65 (with accessory) conforming to IEC 60529 IP23 conforming to IEC 60529	
[Us] Rated Supply Voltage	pply Voltage 12 V AC/DC	
Light Source	High luminosity LED, green	

# Complementary

Material	ABS (acrylonitrile butadiene-styrene): body part PC: globe	
Cad Overall Width	84 mm	
Cad Overall Depth	84 mm	
Net Weight	0.3 kg	
Marking	g CE	
Product Mounting	By 3 M4 screws	
Supply Voltage Limits	1015 V DC 10.813.2 V AC	
[Uimp] Rated Impulse Withstand Voltage	0.8 kV	
Current Consumption	sumption 250 mA	
Flashing Frequency	2.3 Hz	
Clamping Connection Capacity	Connection Capacity 0.83 mm <sup>2</sup>	
Awg Gauge	AWG 18	
Cable Length	500 mm	

#### **Environment**

Standards	EN 61000-6-4 EN 61000-6-2
Product Certifications	UL
Protective Treatment	TC

Ambient Air Temperature For Storage	-3570 °C
Ambient Air Temperature For Operation	-1050 °C
Electrical Shock Protection Class	Class II conforming to IEC 61140

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


# XVR08J03

#### **Dimensions Drawings**

#### Rotating Mirror Beacon

#### **Dimensions**





# **Product datasheet**

# XVR08J03

Mounting and Clearance

# Rotating Mirror Beacon

#### **Panel Cut-out**

