

Product datasheet

Specifications



key selector switch head - 2 pos. - stay put - withdrawal left-hand position

Local distributor code:
2203520

ZA2BG2

EAN Code: 3389110648621

Main

Range Of Product	Harmony XAC
Product Or Component Type	Selector switch
Component Name	ZA2
Product Compatibility	XACA

Complementary

Net Weight	0.042 kg
Cap/Operator Or Lens Colour	Black
Marking	Unmarked
Mounting Location	Front of enclosure Base of enclosure
Sale Per Indivisible Quantity	1

Environment

Standards	IEC 60947-5-1 CSA C22.2 No 14 UL 508 IEC 60204-32
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	100 gn conforming to IEC 60068-2-27
Overvoltage Category	Class II conforming to IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	7.2 cm
Package 1 Length	9.8 cm
Package 1 Weight	50.0 g
Unit Type Of Package 2	BB1

Number Of Units In Package 2	10
Package 2 Height	6.0 cm
Package 2 Width	17.0 cm
Package 2 Length	28.0 cm
Package 2 Weight	508.0 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	50
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	2.864 kg

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)
