

Product datasheet

Specifications



key selector switch head - 2 pos. -
spring return - withdrawal left-hand
pos.

Local distributor code:
386310061

ZA2BG6

EAN Code: 3389110648645

Main

Range Of Product	Harmony XAC
Product Or Component Type	Selector switch
Component Name	ZA2
Product Compatibility	XACA

Complementary

Net Weight	0.042 kg
Cap/Operator Or Lens Colour	Black
Marking	Unmarked
Mounting Location	Front of enclosure
Sale Per Indivisible Quantity	1

Environment

Standards	CSA C22.2 No 14 UL 508 EN/IEC 60204-32 EN/IEC 60947-5-1
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	100 gn conforming to IEC 60068-2-27
Overvoltage Category	Class II conforming to IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 50102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	3.000 cm
Package 1 Length	6.000 cm
Package 1 Weight	51.000 g
Unit Type Of Package 2	BB1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	10
Package 2 Height	3.000 cm
Package 2 Width	13.000 cm
Package 2 Length	15.000 cm
Package 2 Weight	516.000 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	50
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	2.894 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration