

Product datasheet

Specifications



round head for pushbutton - spring return - XAC-A - red - booted

Local distributor code:

2220231

XACA9414

EAN Code: 3389110645163

Main

Range Of Product	Harmony XAC
Product Or Component Type	Head for push-button
Component Name	XACA

Complementary

Marking	Unmarked
Operator Additional Information	Booted
Cap/Operator Or Lens Colour	Red
Product Compatibility	XACA..
Mounting Location	Front of enclosure
Sale Per Indivisible Quantity	10
Standards	CSA C22.2 No 14 UL 508 IEC 60204-32 IEC 60947-5-1
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	100 gn conforming to IEC 60068-2-27
Overvoltage Category	Class II conforming to IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Net Weight	0.01 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	2.3 cm
Package 1 Length	2.5 cm
Package 1 Weight	9.0 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	10

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	3.0 cm
Package 2 Width	7.5 cm
Package 2 Length	11.0 cm
Package 2 Weight	94.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	700
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	7.068 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Circularity Profile	No need of specific recycling operations	