



drilled front plate - XAP-E - metal -2 horizontal openings

Local distributor code: 386425697

XAPE302

EAN Code: 3389110628029

Main

Range Of Product	Harmony XAP	
Product Or Component Type	Front plate with fixing screws	
Device Short Name	XAPE	
Product Destination	For Ø 22 mm control and signalling units	
Product Front Plate Size	72 x 105 mm	
Number Of Cut-Out	2 cut-outs	
Material	Anodised aluminium	
Device Mounting	Flush	
Ip Degree Of Protection IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010		
Resistance To Chemical Agents	Good resistant to acetone Good resistant to alcohols Good resistant to chloride and fluoride solvents Good resistant to diluted mineral acids Good resistant to oils and petrol Good resistant to organic acids Good resistant to salts	

Complementary

Net Weight	0.075 kg
------------	----------

Environment

Protective Treatment	TC TH
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2570 °C
Overvoltage Category	Class I conforming to IEC 60536 Class I conforming to NF C 20-030

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	12.6 cm
Package 1 Length	16.3 cm
Package 1 Weight	92.0 g

Unit Type Of Package 2	S02
Number Of Units In Package 2	30
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.107 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	


Dimensions Drawings

Dimensions and Fixing

Below drawing shows a front plate with 4 cut-outs. Refer to the product characteristics to get the number of cut-outs.



Panel cut-out



b		b1		Н	
mm	in.	mm	in.	mm	in.
105	4.13	77	3.03	89	3.50