Product datasheet

Specifications





junction box for advanced handheld terminal

Local distributor code: 395514418

XBTZGJBOX

EAN Code: 3595864003191

Main

Range Of Product	Magelis XBTGH
Product Or Component Type	Junction box
Product Specific Application	For XBTGH advanced hand-held panel

Complementary

[Us] Rated Supply Voltage	24 V DC
Supply Voltage Limits	19.228.8 V
Inrush Current	30 A
Power Consumption In W	6.3 W
Electrical Connection	1 connector 24-pin connector hand-held panel 1 connector RJ45 Ethernet TCP/IP 1 male connector SUB-D 9 RS232C/RS422/RS485 <= 115.2 kbits/s COM1 serial link Screw terminal block 24 inputs/outputs
Port Ethernet	10BASE-T/100BASE-TX
Enclosure Material	PPT
Fixing Mode	By 4 M4 screws, mounting on 1.5 to 10 mm thick panel Clip-on, mounting on 35 mm symmetrical DIN rail
Marking	CE

Environment

Immunity To Microbreaks	10 ms
Standards	FCC Class A EN 61131-2 IEC 61000-6-2 UL 508
Product Certifications	cULus C-Tick
Ambient Air Temperature For Operation	050 °C
Ambient Air Temperature For Storage	-2060 °C
Operating Altitude	<= 2000 m
Ip Degree Of Protection	IP20 (rear panel) IP65 (front panel)
Shock Resistance	15 gn for 11 ms conforming to IEC 60068-2-27
Vibration Resistance	1 gn (f = 9150 Hz) 3.5 mm (f = 59 Hz)
Relative Humidity	090 % without condensation or dripping water

Resistance To Electrostatic Discharge	6 kV conforming to IEC 61000-4-2 level 3
Resistance To Electromagnetic Fields	10 V/m conforming to IEC 61000-4-3
Resistance To Fast Transients	2 kV conforming to IEC 61000-4-4 level 3

Packing Units

Unit Type Of Package 1PCENumber Of Units In Package 11Package 1 Height17.000 cmPackage 1 Width22.500 cmPackage 1 Length27.000 cmPackage 1 Weight1.184 kg	
Package 1 Height 17.000 cm Package 1 Width 22.500 cm Package 1 Length 27.000 cm Package 1 Weight 1.184 kg	
Package 1 Width 22.500 cm Package 1 Length 27.000 cm Package 1 Weight 1.184 kg	
Package 1 Length 27.000 cm Package 1 Weight 1.184 kg	
Package 1 Weight 1.184 kg	
Unit Type Of Package 2 S03	
Number Of Units In Package 2 2	
Package 2 Height 30.000 cm	
Package 2 Width 30.000 cm	
Package 2 Length 40.000 cm	
Package 2 Weight 2.900 kg	

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information