



# **INDICATING BEACON 48VDC** 10W +OPTIONS

Local distributor code: 398332309

XVBL4B8

! Discontinued on: 9 Feb 2023

EAN Code: 3389110844238

(!) Discontinued

#### Main

Range Of Product	Harmony XVB Universal
Product Or Component Type	Complete beacon
Beacon Or Indicator Bank Unit Type	Base unit direct or tube fixing Illuminated unit
Signalling Type	Flashing
Mounting Diameter	70 mm
Component Name	XVBL
Material	Glass reinforced polyamide: base unit Polycarbonate: illuminated unit
Light Source	Bulb not included, yellow
Bulb Type	Incandescent Incandescent with BA 15d base Protected LED
[Us] Rated Supply Voltage	24 V AC 2448 V DC
Maximum Bawar Dissination In W	711/

Maximum Power Dissipation In W

### Complementary

Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm² with cable end
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1
Nominal Voltage Limit	0.851.1 Un conforming to IEC 60947-5-1
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1
Flashing Frequency	1 Hz
Cad Overall Width	70 mm
Cad Overall Height	139 mm
Cad Overall Depth	70 mm
Terminals Description Iso N°1	(GND)GROUND (COM-1)PW
Net Weight	0.28 kg

#### **Environment**

**Pollution Degree** 

2

Product Certifications	CCC EAC CSA C22-2 No 14 UL 508	
Standards	EN/IEC 60947-5-1	
Protective Treatment	TC	
Ambient Air Temperature For Storage	-4070 °C	
Electrical Shock Protection Class	Class I on support tube conforming to IEC 61140 Class II on base unit conforming to IEC 61140	
Ip Degree Of Protection	IP65 on fixing base XVBZ0. conforming to IEC 60529 IP66 on base unit conforming to IEC 60529	
Nema Degree Of Protection	Type 4X conforming to UL (indoor)	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	8.0 cm
Package 1 Length	14.5 cm
Package 1 Weight	274.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	18
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.4 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

### XVBL4B8

**Dimensions Drawings** 

### Illuminated Beacon for BA 15d Bulb or LED

#### **Dimensions**



### **Product datasheet**

### XVBL4B8

Connections and Schema

### Illuminated Beacon

### Wiring Diagram

