Product datasheet





CLEAR STROBE BEACON 5 JOULE, 230V AC

Local distributor code: 398332529

XVBL6M7

! Discontinued on: 9 Feb 2023

EAN Code: 3389110844948

(!) Discontinued

Main

Range Of Product	Harmony XVB Universal	
Product Or Component Type	Complete beacon	
Beacon Or Indicator Bank Unit Type	Base unit direct or tube fixing Illuminated unit	
Signalling Type	Flashing	
Mounting Diameter	70 mm	
Component Name	XVBL	
Material	Glass reinforced polyamide: base unit Polycarbonate: illuminated unit	
Light Source	Integral flash discharge tube, clear	
Bulb Type	Flash discharge tube	
[Us] Rated Supply Voltage	230 V AC	

Complementary

Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm² with cable end
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1
Nominal Voltage Limit	0.851.1 Un conforming to IEC 60947-5-1
Current Consumption	< 105 mA AC
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1
Flash Energy	5 J
Flashing Frequency	1 Hz
Illuminating Intensity	13 cd
Cad Overall Width	70 mm
Cad Overall Height	232 mm
Cad Overall Depth	70 mm
Terminals Description Iso N°1	(GND)GROUND (COM-1)PW
Net Weight	0.435 kg

Environment

Product Certifications	CCC EAC CSA C22-2 No 14 UL 508	
Standards	IEC 60947-5-1	
Protective Treatment	TC	
Ambient Air Temperature For Storage	-4070 °C	
Electrical Shock Protection Class	Class I on support tube conforming to IEC 61140 Class II on base unit conforming to IEC 61140	
Ip Degree Of Protection	IP65 on fixing base XVBZ0. conforming to IEC 60529 IP66 on base unit conforming to IEC 60529	
Nema Degree Of Protection	Type 4X conforming to UL (indoor)	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.2 cm
Package 1 Width	8.0 cm
Package 1 Length	8.0 cm
Package 1 Weight	435.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.933 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

XVBL6M7

Dimensions Drawings

Illuminated Beacon with "Flash" Discharge Tube Unit

Dimensions



Product datasheet

XVBL6M7

Connections and Schema

Illuminated Beacon

Wiring Diagram

