



# Ø 45 mm tower light - steady - yellow - IP40

XVDLS38

Discontinued on: 17 Apr 2020

EAN Code: 3389110110722

! Discontinued

#### Main

Range Of Product	Harmony XVD Optimum
Product Or Component Type	Complete miniature beacon
Beacon Or Indicator Bank Unit Type	Base unit direct fixing Illuminated unit
Signalling Type	Steady
Mounting Diameter	45 mm
Component Name	XVDLS
Material	Glass reinforced polyamide: base unit Polycarbonate: illuminated unit
Light Source	Bulb not included, yellow
Bulb Type	Incandescent with BA 15d base
[Us] Rated Supply Voltage	<= 230 V
Maximum Power Dissipation In W	5 W

# Complementary

Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm <sup>2</sup> with cable end
Cable Entry	1 entry tapped for Pg 7
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1
Cad Overall Width	45 mm
Cad Overall Height	104 mm
Cad Overall Depth	45 mm
Terminals Description Iso N°1	(COM-1)PW (GND)GROUND
Net Weight	0.08 kg

### **Environment**

Product Certifications	CSA UL
Standards	EN/IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Operation	-2570 °C

Ambient Air Temperature For Storage	-4070 °C
Electrical Shock Protection Class	Class II conforming to IEC 60536
Ip Degree Of Protection	IP40 conforming to IEC 60529

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
<b>Environmental Disclosure</b>	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

## XVDLS38

**Dimensions Drawings** 

### Illuminated Beacon

#### **Dimensions**



# **Product datasheet**

## XVDLS38

Mounting and Clearance

#### Illuminated Beacon

#### **Panel Cut-out for Direct Fixing**

