Product datasheet

Specifications





LENS PILOT LIGHT

Local distributor code: 21160974

ZA2BV07

EAN Code: 3389110648287

Main

Range Of Product	Harmony
Product Or Component Type	Head for pilot light
Product Specific Application	For incandescent bulb
Cap/Operator Or Lens Colour	Clear

Complementary

Mechanical Durability	1000000 cycles	
Net Weight	0.015 kg	
Compatibility Code	ZA2B	

Environment

Standards	EN/IEC 60947-5-1 CSA C22.2 No 14	
Protective Treatment	тн	
Ambient Air Temperature For Operation	-2555 °C	
Ambient Air Temperature For Storage	-4070 °C	
Vibration Resistance	15 gn (f= 10500 Hz) conforming to IEC 60068-2-6	
Shock Resistance	100 gn conforming to IEC 60068-2-27	
Electrical Shock Protection Class	ck Protection Class Class II conforming to IEC 61140	
Overvoltage Category	Class II conforming to IEC 61140	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	gree Of Protection IK08 conforming to EN 50102	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	3.0 cm
Package 1 Length	3.8 cm
Package 1 Weight	16.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10

Package 2 Height	4.0 cm
Package 2 Width	16.0 cm
Package 2 Length	16.0 cm
Package 2 Weight	166.0 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	100
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	1.876 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration