




Price* : 35.46 GBP



Main

Range	Prisma
Range compatibility	Prisma G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	<p>Compact : fixed INS250 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INV250 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed NSX100...160 with earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX250 with earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX100...160 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX250 without earth leakage protection - control: toggle - vertical installation</p> <p>Easypact : fixed CVS100...160 without earth leakage protection - control: toggle - vertical installation</p> <p>Easypact : fixed CVS250 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed INV100 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INV160 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INV200 - control: direct front rotary handle - vertical installation</p> <p>Easypact : fixed CVS100...160 with earth leakage protection - control: toggle - vertical installation</p> <p>Easypact : fixed CVS250 with earth leakage protection - control: toggle - vertical installation</p>
Poles description	<p>1 x 3P : fixed : INS250 vertical installation</p> <p>1 x 3P : fixed : INV250 vertical installation</p> <p>1 x 4P : fixed : INS250 vertical installation</p> <p>1 x 4P : fixed : INV250 vertical installation</p> <p>4 x 3P : fixed : NSX100...160 vertical installation</p> <p>4 x 3P : fixed : NSX250 vertical installation</p> <p>4 x 3P : fixed : CVS100...160 vertical installation</p> <p>4 x 3P : fixed : CVS250 vertical installation</p> <p>1 x 3P : fixed : INV100 vertical installation</p> <p>1 x 3P : fixed : INV160 vertical installation</p> <p>1 x 3P : fixed : INV200 vertical installation</p> <p>3 x 4P : fixed : NSX100...160 vertical installation</p> <p>3 x 4P : fixed : NSX250 vertical installation</p> <p>3 x 4P : fixed : CVS100...160 vertical installation</p> <p>3 x 4P : fixed : CVS250 vertical installation</p> <p>1 x 4P : fixed : INV100 vertical installation</p> <p>1 x 4P : fixed : INV160 vertical installation</p> <p>1 x 4P : fixed : INV200 vertical installation</p>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Complementary

Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Number of vertical modules [50 mm]	<p>8 module(s) : INS250, direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>8 module(s) : INS250, direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>8 module(s) : INV250, direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>8 module(s) : INV250, direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>9 module(s) : CVS100...160 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>9 module(s) : CVS100...160 without earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>11 module(s) : CVS250 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>11 module(s) : CVS250 without earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>8 module(s) : INV100, direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>8 module(s) : INV100, direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>8 module(s) : INV160, direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>8 module(s) : INV160, direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>8 module(s) : INV200, direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>8 module(s) : INV200, direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>9 module(s) : NSX100...160 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>9 module(s) : NSX100...160 without earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>11 module(s) : NSX250 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>11 module(s) : NSX250 without earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>10 module(s) : CVS100...160 with earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>10 module(s) : CVS100...160 with earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s) : CVS250 with earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s) : CVS250 with earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>10 module(s) : NSX100...160 with earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>10 module(s) : NSX100...160 with earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s) : NSX250 with earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s) : NSX250 with earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p>
Condition of using cable tie	Need additional plate (1M high) when installation of device is in vertical
Height	150 mm
Product weight	0.915 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

Standards	IEC 61439-2
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------