

Product datasheet

Specifications



trip unit MicroLogic 6.3 E-M for ComPact NSX 400/630 circuit breakers, electronic, rating 320 A, 3 poles 3d

Local distributor code:

391356324

LV432075

❗ Discontinued

❗ Discontinued on: 9 Aug 2023

Important message: This product has been switched to new ComPacT range and is no longer commercialized.
EAN Code: 3606480017599

Main

Range	ComPact
Range Of Product	ComPact NSX400...630
Product Or Component Type	Trip unit
Trip Unit Name	MicroLogic 6.3 E-M
Trip Unit Technology	Electronic
Range Compatibility	ComPact NSX400 ComPact NSX630
Device Application	Motor
Number Of Poles	3P
Protected Poles Description	3t
Trip Unit Protection Functions	LSIG
Protection Type	L : for overload protection (long time) S : for short time short-circuit protection I : for instantaneous short-circuit protection G : for ground fault protection
Trip Unit Rated Current	320 A at 65 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz

Complementary

Motor Tripping Class	30 10 20 5
Complementary Motor Protection	Protracted starting time Current unbalance Underload Stalled rotor
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	160...320 A
Long-Time Protection Delay Adjustment Type Tr	Adjustable

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Tr] Long-Time Protection Delay Adjustment Range	120 s at 1.5 x Ir for trip class 5 6.5 s at 6 x Ir for trip class 5 5 s at 7.2 x Ir for trip class 5 240 s at 1.5 x Ir for trip class 10 13.5 s at 6 x Ir for trip class 10 10 s at 7.2 x Ir for trip class 10 480 s at 1.5 x Ir for trip class 20 26 s at 6 x Ir for trip class 20 20 s at 7.2 x Ir for trip class 20 720 s at 1.5 x Ir for trip class 30 38 s at 6 x Ir for trip class 30 30 s at 7.2 x Ir for trip class 30
Thermal Memory	20 minutes before and after tripping
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable 9 settings
[Isd] Short-Time Protection Pick-Up Adjustment Range	5...13 x Ir
Short-Time Protection Delay Adjustment Type Tsd	Fixed
[Tsd] Short-Time Protection Delay Adjustment Range	0.01 s
Instantaneous Protection Pick-Up Adjustment Type Ii	Fixed
[Ii] Instantaneous Protection Pick-Up Adjustment Range	4800 A
Ground-Fault Protection Pick-Up Adjustment Type Ig	Adjustable
[Ig] Ground-Fault Protection Pick-Up Adjustment Range	0.2...1 x In for In > 50 A 0.3...1 x In for In = 50 A 0.6...1 x In for In = 25 A Ig enable on/off
Ground-Fault Protection Time Delay Adjustment Type Tg	Adjustable
[Tg] Ground-Fault Protection Time Delay Adjustment Range	0...0.4 s
Earth-Leakage Protection	Without
Zone Selective Interlocking Zsi	With
Local Signalling	Flashing LED (green) for ready to operate LED 95 % lth (red) for temperature over set point
Display Type	LCD display
Type Of Measurement	Energy meter
Electrical Data Recording	Maintenance indicators

Environment

Standards	EN/IEC 60947-2 UL 508
Product Certifications	CCC Marine EAC
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.4 cm
Package 1 Width	19.0 cm

Package 1 Length	21.9 cm
Package 1 Weight	1.501 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	10
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	15.776 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information