



### Main

Range	Prisma
Range compatibility	Prisma G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	<p>Easypact : fixed EZC400 - control: toggle - vertical installation</p> <p>Easypact : fixed CVS400 without earth leakage protection - control: toggle - vertical installation</p> <p>Easypact : fixed CVS630 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed INS320...400 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INS500...630 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INV320...400 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INV500...630 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed NSX400 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX630 without earth leakage protection - control: toggle - vertical installation</p> <p>Easypact : fixed CVS400 with earth leakage protection - control: toggle - vertical installation</p> <p>Easypact : fixed CVS630 with earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX400 with earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX630 with earth leakage protection - control: toggle - vertical installation</p> <p>Easypact : fixed EZC630 - control: toggle - vertical installation</p>
Poles description	<p>1 x 3P : fixed : NSX400 vertical installation</p> <p>1 x 3P : fixed : NSX630 vertical installation</p> <p>1 x 3P : fixed : EZC400 vertical installation</p> <p>1 x 3P : fixed : EZC630 vertical installation</p> <p>1 x 3P : fixed : CVS400 vertical installation</p> <p>1 x 3P : fixed : CVS630 vertical installation</p> <p>1 x 3P : fixed : INS320...400 vertical installation</p> <p>1 x 3P : fixed : INS500...630 vertical installation</p> <p>1 x 3P : fixed : INV320...400 vertical installation</p> <p>1 x 3P : fixed : INV500...630 vertical installation</p> <p>1 x 4P : fixed : NSX400 vertical installation</p> <p>1 x 4P : fixed : NSX630 vertical installation</p> <p>1 x 4P : fixed : EZC400 vertical installation</p> <p>1 x 4P : fixed : EZC630 vertical installation</p> <p>1 x 4P : fixed : CVS400 vertical installation</p> <p>1 x 4P : fixed : CVS630 vertical installation</p> <p>1 x 4P : fixed : INS320...400 vertical installation</p> <p>1 x 4P : fixed : INS500...630 vertical installation</p> <p>1 x 4P : fixed : INV320...400 vertical installation</p>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Complementary

Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Number of vertical modules [50 mm]	<p>12 module(s) : CVS400 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s) : CVS400 without earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s) : CVS630 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s) : CVS630 without earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s) : EZC400, direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s) : EZC400, direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s) : EZC630, direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s) : EZC630, direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>10 module(s) : INS320...400, direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>10 module(s) : INS320...400, direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s) : INS500...630, direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s) : INS500...630, direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>10 module(s) : INV320...400, direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>10 module(s) : INV320...400, direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s) : INV500...630, direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s) : INV500...630, direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s) : NSX400 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s) : NSX400 without earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s) : NSX630 without earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s) : NSX630 without earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>14 module(s) : CVS400 with earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>14 module(s) : CVS400 with earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>15 module(s) : CVS630 with earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>15 module(s) : CVS630 with earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>14 module(s) : NSX400 with earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>14 module(s) : NSX400 with earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>15 module(s) : NSX630 with earth leakage protection , direct with long terminal shield in 600 mm Wide floor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>15 module(s) : NSX630 with earth leakage protection , direct with long terminal shield in 600 mm Wide wall-mounted enclosure (cable coming from top or bottom of enclosure)</p>
Condition of using cable tie	Need additional plate (1M high) when installation of device is in vertical
Height	300 mm
Product weight	2.64 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

## Environment

Standards	IEC 61439-2
Product certifications	ASEFA

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------