Product datasheet





FRONT PLATE TARIF NSX250 W600 9M

03258

! Discontinued on: 9 Aug 2023

EAN Code: 3303430032588

(!) Discontinued

Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed INV100 - control: direct front rotary handle - vertical installation ComPact: fixed INV160 - control: direct front rotary handle - vertical installation ComPact: fixed INV200 - control: direct front rotary handle - vertical installation ComPact: fixed INV250 - control: direct front rotary handle - vertical installation ComPact: fixed NSX100160 without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX250 without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX250 with earth leakage protection - control: toggle - vertical installation
Poles Description	1 x 4P: mounting plate support: INV100 vertical installation 1 x 4P: mounting plate support: INV160 vertical installation 1 x 4P: mounting plate support: INV200 vertical installation 1 x 4P: mounting plate support: INV250 vertical installation 1 x 4P: mounting plate support: INV250 vertical installation 1 x 4P: mounting plate support: NSX100160 vertical installation 1 x 4P: mounting plate support: NSX250 vertical installation
Operating Position	Superposed

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 + 150 mm depth 400 mm
Number Of Vertical Modules [50 Mm]	9
Standards	IEC 61439-1 NF C 15-100 IEC 61439-2
Product Certifications	ASEFA
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	450 mm

Life Is On Schneider 24 Apr 2024



Width	600 mm
Net Weight	1.7 kg
Quantity Per Set	Set of 1
Functional Unit	600 mm Prisma G floor-standing enclosure ComPact INV100 fixed direct front rotary handle vertical 4P 1 direct 600 mm Prisma G wall-mounted enclosure ComPact INV100 fixed direct front rotary handle vertical 4P 1 direct 650 + 150 mm 400 mm Prisma P cubicle ComPact INV100 fixed direct front rotary handle vertical 4P 1 direct 600 mm Prisma G floor-standing enclosure ComPact INV160 fixed direct front rotary handle vertical 4P 1 direct 600 mm Prisma G wall-mounted enclosure ComPact INV160 fixed direct front rotary handle vertical 4P 1 direct 650 + 150 mm 400 mm Prisma P cubicle ComPact INV160 fixed direct front rotary handle vertical 4P 1 direct 600 mm Prisma G floor-standing enclosure ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct 600 mm Prisma G wall-mounted enclosure ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct 600 mm Prisma G wall-mounted enclosure ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct 650 + 150 mm 400 mm Prisma P cubicle ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct 600 mm Prisma G floor-standing enclosure ComPact INV250 fixed direct front rotary handle vertical 4P 1 direct 600 mm Prisma G wall-mounted enclosure ComPact INV250 fixed direct front rotary handle vertical 4P 1 direct 600 mm Prisma G wall-mounted enclosure ComPact INV250 fixed direct front rotary handle vertical 4P 1 direct 650 + 150 mm 400 mm Prisma P cubicle ComPact NSX100160 without fixed toggle vertical 4P 1 direct 650 + 150 mm 400 mm Prisma P cubicle ComPact NSX250 without fixed toggle vertical 4P 1 direct 650 + 150 mm 400 mm Prisma P cubicle ComPact NSX250 without fixed toggle vertical 4P 1 direct 650 + 150 mm 400 mm Prisma P cubicle ComPact NSX250 without fixed toggle vertical 4P 1 direct 600 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed toggle vertical 4P 1 direct 600 mm Prisma G wall-mounted enclosure ComPact NSX250 without fixed toggle vertical 4P 1 direct 600 mm Prisma G wall-mounted enclosure ComPact NSX250 with fixed

Environment

Ip Degree Of Protection	IP30		

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	46 cm
Package 1 Length	51 cm
Package 1 Weight	1.71 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	10 cm
Package 2 Width	52 cm
Package 2 Length	53 cm

Package 2 Weight	10.64 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	24
Package 3 Height	35 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	42.56 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
②	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile