Product datasheet

Specifications





Acti9 - IHH - mechanical time switch - 7 days - 150 h memory

Local distributor code: 391264937

15331

EAN Code: 3303430153313

Main

Range Of Product	Acti9
Product Name	Acti9 IHH
Device Short Name	ІНН
Product Or Component Type	Mechanical time switch
Number Of Channels	1
Function Available	Manual time changeover

Complementary

Complementary		
Device Application	Building	
Load Type	Parallel-corrected fluorescent tube 5 x 58 W 4.7 μF Parallel-corrected fluorescent tube 7 x 40 W 7 μF Parallel-corrected fluorescent tube 2 x 100 W 18 μF 230 V AC halogen lamp 1000 W 230 V AC incandescent lamp 1000 W Fluocompact lamp 700 VA Compact fluorescent lamp 150 W LED lamp < 2 W 30 W LED lamp > 2 W 300 W	
Cycle Duration	7 days	
Maximum Number Of Switchings	42 on - 42 off	
Minimum Interval Duration	2 h	
Type Of Setting	Manual time changeover	
Measurement Accuracy	+/- 1 s/day 20 °C	
Power Consumption In W	0.5 W	
Maximum Switching Current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6	
[Ue] Rated Operational Voltage	230240 V AC at 5060 Hz	
Battery Life	10 year(s)	
Backup Time	150 h time and program saving	
Mounting Support	DIN rail	
9 Mm Pitches	2	
Colour Tint	White (RAL 9003)	
Connections - Terminals	Screw terminals	
Width	18 mm	
Height	90 mm	
Depth	66 mm	

Net Weight	0.101 kg
Environment	
Ambient Air Temperature For Operation	-1050 °C
Ip Degree Of Protection	Terminals: IP20 B
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	7.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	89.0 g
Unit Type Of Package 2	\$03
Number Of Units In Package 2	100
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm

Contractual warranty

Warranty

Package 2 Length

Package 2 Weight

18 months

40.0 cm

9.452 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information