


Product datasheet

Specifications



Mounting Plate Vert. Withd. NT-MTZ1/NS 3P/4P 1600A W650 Prisma P

03483

⚠ Discontinued on: 5 Apr 2023

⚠ Discontinued

EAN Code: 3303430034834

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Installation Description	Cubicle - width 650 mm depth 400 mm Cubicle - width 650 mm depth 800 mm
Installed Device	ComPact: drawout NS1250 - control: toggle - vertical installation ComPact: drawout NS1250 - control: direct front rotary handle - vertical installation ComPact: drawout NS1250 - control: motor mechanism - vertical installation ComPact: drawout NS1600 - control: toggle - vertical installation ComPact: drawout NS1600 - control: direct front rotary handle - vertical installation ComPact: drawout NS1600 - control: motor mechanism - vertical installation ComPact: drawout NS630b...1000 - control: toggle - vertical installation ComPact: drawout NS630b...1000 - control: direct front rotary handle - vertical installation ComPact: drawout NS630b...1000 - control: motor mechanism - vertical installation Masterpact: drawout NT06...10 - control: toggle - vertical installation Masterpact: drawout NT06...10 - control: motor mechanism - vertical installation Masterpact: drawout NT12 - control: toggle - vertical installation Masterpact: drawout NT12 - control: motor mechanism - vertical installation Masterpact: drawout NT16 - control: toggle - vertical installation Masterpact: drawout NT16 - control: motor mechanism - vertical installation
Poles Description	1 x 3P: drawout NS1250 vertical installation 1 x 4P: drawout NS1250 vertical installation 1 x 3P: drawout NS1600 vertical installation 1 x 4P: drawout NS1600 vertical installation 1 x 3P: drawout NS630b...1000 vertical installation 1 x 4P: drawout NS630b...1000 vertical installation 1 x 3P: drawout NT06...10 vertical installation 1 x 4P: drawout NT06...10 vertical installation 1 x 3P: drawout NT12 vertical installation 1 x 4P: drawout NT12 vertical installation 1 x 3P: drawout NT16 vertical installation 1 x 4P: drawout NT16 vertical installation

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Vertical Modules [50 Mm]	16 module(s): NS1250, rear connection on Canalis in 650 mm Widecubicle 16 module(s): NS1600, rear connection on Canalis in 650 mm Widecubicle 16 module(s): NS630b...1000, rear connection on Canalis in 650 mm Widecubicle 18 module(s): NS1250, front connection on Canalis in 650 mm Widecubicle 15 module(s): NS1250, front connection on adaptor in 650 mm Widecubicle 11 module(s): NS1250, rear connection on adaptor in 650 mm Widecubicle 15 module(s): NS1600, front connection on adaptor in 650 mm Widecubicle 11 module(s): NS1600, rear connection on adaptor in 650 mm Widecubicle 18 module(s): NS630b...1000, front connection on Canalis in 650 mm Widecubicle 13 module(s): NS630b...1000, front connection on adaptor in 650 mm Widecubicle 11 module(s): NS630b...1000, rear connection on adaptor in 650 mm Widecubicle 13 module(s): NT06...10, front connection on adaptor in 650 mm Widecubicle 11 module(s): NT06...10, rear connection on adaptor in 650 mm Widecubicle 18 module(s): NT06...10, front connection on Canalis in 650 mm Widecubicle 16 module(s): NT06...10, rear connection on Canalis in 650 mm Widecubicle 15 module(s): NT12, front connection on adaptor in 650 mm Widecubicle 11 module(s): NT12, rear connection on adaptor in 650 mm Widecubicle 18 module(s): NT12, front connection on Canalis in 650 mm Widecubicle 16 module(s): NT12, rear connection on Canalis in 650 mm Widecubicle 15 module(s): NT16, front connection on adaptor in 650 mm Widecubicle 11 module(s): NT16, rear connection on adaptor in 650 mm Widecubicle 16 module(s): NT16, rear connection on Canalis in 650 mm Widecubicle
Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	650 mm
Height	30 mm
Net Weight	3.2 kg

[illegible]

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	17.5 cm
Package 1 Length	57 cm
Package 1 Weight	3.2 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Mercury Free	
✓	RoHS Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Eu RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information