



15365 has not been replaced. Please contact your customer care centre for more information.

Main

Range of product	Multi 9
Product name	Multi 9 IH
Device short name	IH
Product or component type	Mechanical switch
Number of channels	1
Function available	Manual time changeover

Complementary

Device application	Building
Load type	1 parallel-corrected fluorescent tube conventional ballast (58 W) 10 non-corrected fluorescent tube conventional ballast (58 W) 10 serial-corrected fluorescent tube conventional ballast (58 W) 15 non-corrected fluorescent tube conventional ballast (40 W) 15 serial-corrected fluorescent tube conventional ballast (40 W) 2 parallel-corrected fluorescent tube conventional ballast (40 W) 230 V AC halogen lamp (1100 W) 230 V AC incandescent lamp (1100 W) 3 dual mounted fluorescent tube conventional ballast (2 x 100 W) 5 dual mounted fluorescent tube conventional ballast (2 x 58 W) 6 non-corrected fluorescent tube conventional ballast (100 W) 6 serial-corrected fluorescent tube conventional ballast (100 W)
Cycle duration	24 h
Measurement accuracy	+/- 1 s/day
Maximum number of switchings	24 on - 24 off
Minimum interval duration	30 min
Type of setting	Manual time changeover
Measurement accuracy	+/- 1 s/day
Power consumption in VA	2.5 VA
Maximum switching current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	230 V AC +/- 10 % at 50/60 Hz
Backup time	150 h time and program saving
Mounting support	DIN rail
9 mm pitches	6
Colour tint	White (RAL 9003)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

IP degree of protection	IP20 B
Width	54 mm
Net weight	0.198 kg

Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	Terminals: IP20 B

Contractual warranty

Warranty	18 months
----------	-----------