



Main

Product or component type	Impulse relay
Device short name	TLI
Device application	Remote control
Poles	2P
Pole contact composition	1 NO + 1 NC
[In] rated current	16 A
Network type	AC
[Uc] control circuit voltage	24 V AC 50/60 Hz 12 V DC

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	250 V AC 50/60 Hz
Control type	Coil disconnection Remote control
Control signal type	Impulse
Switching frequency	100 switching operations/day 5 switching operations/minute
Impulse duration	50 ms...1 s
Remote control type	Illuminated push-button 3 mA
Local signalling	ON/OFF indication
Mounting mode	Fixed
Mounting support	DIN rail
9 mm pitches	2
Height	84 mm
Width	18 mm
Depth	60 mm
Electrical durability	AC-21: 200000 cycles AC-22: 100000 cycles
Range compatibility	ATEt ATL

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	EN 669-1 EN 669-2-2
Product certifications	GOST
Quality labels	CEBEC IMQ VDE NF
Noise level	60 dB
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C

Contractual warranty

Warranty	18 months
----------	-----------

15503 is replaced by:



impulse relay A9C30115

impulse relay iTLI - 2P - 1NO+1NC - 16A - coil 12 VDC - 24 VAC 50/60Hz

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2011