



Commercial status

Discontinued: 13 June 2018

⚠ Discontinued

Main

Product or component type	Extension for impulse relay
Device short name	ETL
Relay application	Remote control
Poles description	1P
Pole contact composition	1 NO
[In] rated current	32 A
Network type	AC

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	250 V AC 50/60 Hz
Control type	Remote control Toggle
Control signal type	Impulse
Switching frequency	5 switching operations/minute
Impulse duration	50 ms
Remote control type	Illuminated push-button
Local signalling	ON/OFF indication
[Uc] control circuit voltage	230...240 V AC 50/60 Hz 110 V DC
Supply inrush power	19 VA
Mounting mode	Fixed, on right side of TL
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Height	84 mm
Width	18 mm
Depth	60 mm
Colour	Grey
Electrical durability	AC-21: 50000 cycles AC-22: 20000 cycles
Connections - terminals	Tunnel type terminals
Auxiliary connection terminal	Tunnel type terminals control circuit in 0.5...6 mm ²

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Noise level	60 dB
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C

Contractual warranty

Warranty	18 months
----------	-----------

15505 is replaced by:



electrical auxiliaries A9C32836

extension ETL iTL 32 - 1P -1NO - 32A - coil 110 VDC - 230...240VAC 50/60Hz

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2011