



### Commercial status

Discontinued: 06 August 2018

ⓘ Discontinued

### Main

Product or component type	Impulse relay
Device short name	TL
Device application	Remote control
Poles	1P
Pole contact composition	1 NO
[In] rated current	16 A
Network type	AC
[Uc] control circuit voltage	130 V AC 50/60 Hz 48 V DC

### Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	250 V AC 50/60 Hz
Control type	Coil deconnection Remote control
Control signal type	Impulse
Switching frequency	100 switching operations/day 5 switching operations/minute
Impulse duration	50 ms...1 s
Remote control type	Illuminated push-button 3 mA
Local signalling	ON/OFF indication
Mounting mode	Fixed
Mounting support	DIN rail
9 mm pitches	2
Height	84 mm
Width	18 mm
Depth	60 mm
Electrical durability	AC-21: 200000 cycles AC-22: 100000 cycles
Range compatibility	ATEt ATL

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	EN 669-2-2 EN 669-1
Product certifications	GOST
Quality labels	NF VDE IMQ CEBEC
Noise level	60 dB
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C

## Contractual warranty

Warranty	18 months
----------	-----------

## 15511 is replaced by:



impulse relay A9C30311

impulse relay iTL - 1P - 1NO - 16A - coil 130 VAC 50/60Hz- 48 VDC

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2011