# **Product datasheet**

Specification





## circuit breaker basic frame, ComPact NS 1250N, 50 kA at 415 VAC, 1250 A, fixed, electrically operated, without trip unit, 3 P

Local distributor code: 383449029 333

EAN Code: 3303430333005

#### Main

Range	ComPacT	
Range Of Product	ComPacT NS630b1600 new generation	
Device Short Name	Compact NS1250N	
Product Or Component Type	Basic frame	
Device Application	Distribution	
Number Of Poles	3P	
[In] Rated Current	1250 A at 50 °C	
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz	
Network Type	AC	
Network Frequency	50/60 Hz	
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	
Utilisation Category	Category B	
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	30 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 500/525 V AC 50/60 Hz conforming to IEC 60947-2	
Performance Level	N 50 kA 415 V AC	
Control Type	Electrically operated	
Mounting Mode	Fixed	

### Complementary

•	
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[lcs] Rated Service Short-Circuit Breaking Capacity	30 kA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 (electrical operation) 22 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 (electrical operation) 37 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 (electrical operation) 37 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 (electrical operation) 37 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 (electrical operation)
[Icw] Rated Short-Time Withstand Current	19.2 kA 1 s conforming to IEC 60947-2
Integral Instant Protection	40 kA
Mechanical Durability	10000 cycles conforming to IEC 60947-2
Electrical Durability	2000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 3000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 4000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 5000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2

Power Losses	44 W
Mounting Support	Backplate
Connection Pitch	70 mm
Protection Type	Without protection
Height (H)	327 mm
Width (W)	210 mm
Depth (D)	147 mm

### **Environment**

Standards	IEC 60947-2	
Product Certifications	ASEFA LCIE ASTA	
Pollution Degree	3 conforming to IEC 60947	
Ip Degree Of Protection	IP40 conforming to IEC 60529	
Ik Degree Of Protection	IK07 conforming to EN 50102	
Ambient Air Temperature For Operation	-2570 °C	
Ambient Air Temperature For Storage	-5085 °C	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.0 cm
Package 1 Width	40.0 cm
Package 1 Length	40.0 cm
Package 1 Weight	20.7 kg

### **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>②</b>	Mercury Free	
	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information