Product datasheet

Specifications





circuit breaker basic frame, ComPact NS 1250N, 50 kA at 415 VAC, 1250 A, withdrawable, manually operated, without trip unit, 3 P Local distributor code:

) To be discontinued

33350

() To be discontinued on: 14 Jun 2024

EAN Code: 3303430333500

383460257

Main

| Wall | |
|---|--|
| Range | ComPact |
| Range Of Product | ComPact NS630b1600 |
| Device Short Name | Compact NS1250N |
| Product Or Component Type | Basic frame |
| Device Application | Distribution |
| Number Of Poles | 3P |
| [In] Rated Current | 1250 A at 50 °C |
| [Ue] Rated Operational Voltage | 690 V AC 50/60 Hz |
| Network Type | AC |
| Network Frequency | 50/60 Hz |
| Suitability For Isolation | Yes conforming to EN/IEC 60947-2 |
| Utilisation Category | Category B |
| [Icu] Rated Ultimate Short-Circuit Breaking Capacity | 30 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 |
| Performance Level | N 50 kA 415 V AC |
| Control Type | Rotary handle Toggle |
| Mounting Mode | Drawout |

Complementary

| [Ui] Rated Insulation Voltage | 800 V AC 50/60 Hz conforming to IEC 60947-2 |
|--|---|
| [Uimp] Rated Impulse Withstand Voltage | 8 kV conforming to IEC 60947-2 |
| [Ics] Rated Service Short-Circuit Breaking Capacity | 30 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation) 40 kA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation) 50 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation) 50 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation) 50 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation) |
| [Icw] Rated Short-Time Withstand Current | 19.2 kA 1 s conforming to IEC 60947-2 |
| Integral Instant Protection | 40 kA |

| Mechanical Durability | 10000 cycles conforming to IEC 60947-2 | |
|-----------------------|--|--|
| Electrical Durability | 2000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 3000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 4000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 5000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2 | |
| Power Losses | 84 W | |
| Mounting Support | Backplate | |
| Connection Pitch | 70 mm | |
| Protection Type | Without protection | |
| Height (H) | 327 mm | |
| Width (W) | 210 mm | |
| Depth (D) | 147 mm | |

Environment

| Standards | IEC 60947-2 |
|--|------------------------------|
| Product Certifications | ASEFA ASTA LCIE |
| Pollution Degree | 3 conforming to IEC 60947 |
| Ip Degree Of Protection | IP40 conforming to IEC 60529 |
| Ik Degree Of Protection | IK07 conforming to EN 50102 |
| Ambient Air Temperature For Operation | -2570 °C |
| Ambient Air Temperature For Storage | -5085 °C |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 37.0 cm |
| Package 1 Width | 39.5 cm |
| Package 1 Length | 23.0 cm |
| Package 1 Weight | 14.104 kg |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |