# **Product datasheet**

Specifications





## PratiKa wander plug - straight - 63 A - 3P + N + E - 200...250 V AC -IP67

81380

() Discontinued on: 24 Jul 2020

(!) End-of-service on: 30 Jun 2023

EAN Code: 3303430813804

#### Main

| Range                     | PratiKa      |
|---------------------------|--------------|
| Product Or Component Type | Wander plug  |
| Device Short Name         | PratiKa plug |
| Plug, Socket Category     | Low voltage  |
| Poles Description         | 3P + N + E   |
| Network Type              | AC           |
| Outlet Standard           | Industrial   |

#### Complementary

| oomplemental y                         |   |
|--|---|
| Plug, Socket, Control Station<br>Shape | Straight  |
| [In] Rated Current                     | 63 A  |
| [Ue] Rated Operational Voltage         | 200250 V  |
| Network Frequency                      | 50/60 Hz  |
| Ground Lug Clockwise Position          | 9 h   |
| Plug, Socket Material                  | Housing: self-extinguishing engineering polymer |
| Contacts Material                      | Pins: nickel plated brass                       |
| Connections - Terminals                | Captive screws                                  |
| Cable Cross Section                    | 625 mm <sup>2</sup>                             |
| Cable Outer Diameter                   | 1731 mm   |
| Cable Entry                            | Cable gland                                     |
| Thread Type                            | Pg 36   |
| Net Weight                             | 0.792 kg  |
| Height                                 | 265 mm  |
| Width                                  | 110 mm  |
| Depth                                  | 110 mm  |
| Colour                                 | Grey (RAL 7035)                                 |
| Voltage Colour                         | Blue  |

#### Environment

| Standards                                | IEC 60309-2<br>IEC 60309-1                      |
|--|---|
| Ip Degree Of Protection                  | IP67 conforming to IEC 60529                    |
| Ik Degree Of Protection                  | IK08 conforming to EN 62262                     |
| Fire Resistance                          | 850 °C conforming to IEC 60695-2-11             |
| Relative Humidity                        | 50 % at 40 °C<br>70 % at 30 °C<br>90 % at 20 °C |
| Operating Altitude                       | 2000 m  |
| Ambient Air Temperature For<br>Operation | 35 °C(86400 s)<br>-2540 °C                      |

## **Packing Units**

| Unit Type Of Package 1       | PCE      |
|------------------------------|----------|
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 11.4 cm  |
| Package 1 Width              | 11.4 cm  |
| Package 1 Length             | 24.8 cm  |
| Package 1 Weight             | 800.0 g  |
| Unit Type Of Package 2       | \$03     |
| Number Of Units In Package 2 | 10       |
| Package 2 Height             | 30.0 cm  |
| Package 2 Width              | 30.0 cm  |
| Package 2 Length             | 40.0 cm  |
| Package 2 Weight             | 8.487 kg |

#### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

| Reach Regulation      | REACh Declaration   |
|-----------------------|---|
| Eu Rohs Directive     | Compliant with Exemptions   |
| China Rohs Regulation | China RoHS declaration<br>Product out of China RoHS scope. Substance declaration for your information |
| Circularity Profile   | No need of specific recycling operations  |