# **Product datasheet**





## auxiliary contact, Acti9, iOF/ SD+OF, 2OC, AC/DC

Local distributor code: 396734938 A9A26929

! Discontinued on: 31 Dec 2023

EAN Code: 3606480087882

! Discontinued

#### Main

Range Of Product	Acti9
Product Or Component Type	Double OC or fault contact
Device Short Name	iOF/SD+OF
Signal Contacts Composition	2 C/O
[In] Rated Current	DC-12 1 A at 130 V, DC
	DC-12 1.5 A at 60 V, DC
	DC-12 2 A at 48 V, DC
	DC-12 6 A at 24 V, DC
	AC-12 3 A at 415 V, AC 50/60 Hz
	AC-12 6 A at 240 V, AC 50/60 Hz
Q Mm Pitches	1

9 Mm Pitches

### Complementary

[Ui] Rated Insulation Voltage	500 V
[Himn] Dated Impulse Withstand	4114
[Uimp] Rated Impulse Withstand Voltage	4 kV
Local Signalling	Mechanical indicator
Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	NO
Height	90 mm
Width	9 mm
Depth	73 mm
Net Weight	43 g
Colour	White
Connections - Terminals	Screw clamp terminal (top and bottom) 2 cable(s) 2.5 mm² - rigid Screw clamp terminal (top and bottom) 2 cable(s) 1.5 mm² - flexible with ferrule Screw clamp terminal (top and bottom) 1 cable(s) 0.52.5 mm² - flexible Screw clamp terminal (top and bottom) 1 cable(s) 14 mm² - rigid
Wire Stripping Length	10 mm
Tightening Torque	1 N.m

#### **Environment**

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1

Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-4085 °C

## **Packing Units**

PCE
1
7.500 cm
2.400 cm
9.200 cm
50.000 g
BB1
12
8.500 cm
10.000 cm
27.000 cm
693.000 g
S03
120
30.000 cm
30.000 cm
40.000 cm
7.600 kg

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information