



Main

Range	Acti 9
Product name	Acti 9 iDPN N Vigi
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Device short name	IDPN N Vigi
Device application	Distribution
Poles description	1P + N
Number of protected poles	1
Neutral position	Left
[In] rated current	6 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type A
Breaking capacity	6000 A Icn at 220...240 V AC 50 Hz conforming to EN/IEC 61009-2-1
Suitability for isolation	Yes conforming to EN/IEC 60947-2

Complementary




Device location in system	Outgoer
Network frequency	50 Hz
[Ue] rated operational voltage	220...240 V AC 50 Hz
Magnetic tripping limit	5...10 x In
Residual current tripping technology	Voltage independent
[Ics] rated service breaking capacity	6000 A 100 % x Icn at 220...240 V AC 50 Hz conforming to EN/IEC 61009-2-1
Rated breaking and making capacity	I _{dm} 6000 A at 220...240 V AC 50 Hz conforming to EN/IEC 61009-2-1
Limitation class	3 conforming to EN/IEC 61009-2-1

[Ui] rated insulation voltage	AC 50 Hz
[Uimp] rated impulse withstand voltage	4 kV
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON, OFF, fault trip
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4
Height	85 mm
Width	36 mm
Depth	73 mm
Net weight	125 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	20000 cycles
Locking options description	Padlocking device
Connections - terminals	Single terminal top or bottom1...16 mm ² rigid Single terminal top or bottom1...10 mm ² flexible Single terminal top or bottom1...10 mm ² flexible with ferrule
Wire stripping length	15 mmfor top or bottom connection
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Integrated

Environment

Standards	EN/IEC 61009-2-1
Product certifications	VDE KEMA RCM
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3
Overvoltage category	III conforming to IEC 60364
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to EN/IEC 61009-2-1
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------