



# voltage release - iMX+OF - tripping unit - 48 VAC

A9A26947

EAN Code: 3606480087967



#### Main

Range Of Product	Acti9
Product Or Component Type	Shunt trip release with OC contact
Device Short Name	iMX+OF
Signal Contacts Composition	1 C/O
[In] Rated Current	AC-12 2 A at 48 V, AC 50 Hz DC-12 2 A at 48 V, DC
[Uc] Control Circuit Voltage	48 V AC 50/60 Hz 48 V DC
9 Mm Pitches	2

## Complementary

Range Compatibility	Acti 9 Acti9 iC65 Acti 9 Acti9 iDPN Vigi Acti 9 Acti9 iIDPN Vigi Acti 9 Acti9 iID Acti 9 Acti9 iSW-NA Acti 9 Acti9 iPN (China version) Acti 9 Acti9 iC60 double terminals miniature circuit breaker Acti 9 Acti9 iC40	
Local Signalling	Action indicator	
Mounting Mode	Clip-on	
Mounting Support	DIN rail	
Comb Busbar And Distribution Block Compatibility	Top: YES	
Width	18 mm	
Colour	White	
Connections - Terminals	ions - Terminals  Clamp terminal - 1 cable(s) 5 mm² - rigid  Clamp terminal - 2 cable(s) 2.4 mm² - rigid  Clamp terminal - 1 cable(s) 3 mm² - flexible  Clamp terminal - 2 cable(s) 2.4 mm² - flexible with cable end	
Tightening Torque	1 N.m	
Compatibility Code	IMX+OF	

### **Environment**

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C

Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-4085 °C

## **Packing Units**

PCE
1
3.000 cm
7.900 cm
9.300 cm
80.000 g
BB1
8
8.500 cm
10.000 cm
26.500 cm
700.000 g
S03
72
30.000 cm
30.000 cm
40.000 cm
6.783 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information