

Product datasheet

Specifications



Miniature circuit breaker (MCB), Acti9 iC60a, 1P, 13A, C curve, 4500A (IEC/EN 60898-1), 6kA (IEC/ EN 60947-2)

A9F64113

⚠ Discontinued on: 7 Aug 2023

⚠ Discontinued

EAN Code: 3606480092190

Main

Device Application	Distribution
Range	Acti9
Product Name	Acti9 iC60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	iC60a
Poles Description	1P
Number Of Protected Poles	1
[In] Rated Current	13 A
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	4500 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1 6 kA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2
Utilisation Category	Category A conforming to EN 60947-2 Category A conforming to IEC 60947-2
Suitability For Isolation	Yes conforming to EN 60898-1 Yes conforming to EN 60947-2 Yes conforming to IEC 60898-1 Yes conforming to IEC 60947-2
Standards	IEC 60947-2 EN 60947-2 IEC 60898-1 EN 60898-1

Complementary

Network Frequency	50/60 Hz
Magnetic Tripping Limit	8 x In +/- 20 %
[Ics] Rated Service Breaking Capacity	6 kA 100 % conforming to EN 60947-2 - 220...240 V AC 50/60 Hz 6 kA 100 % conforming to IEC 60947-2 - 220...240 V AC 50/60 Hz 4500 A 100 % conforming to EN 60898-1 - 230 V AC 50/60 Hz 4500 A 100 % conforming to IEC 60898-1 - 230 V AC 50/60 Hz
Limitation Class	3 conforming to EN 60898-1 3 conforming to IEC 60898-1
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz conforming to EN 60947-2 500 V AC 50/60 Hz conforming to IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN 60947-2 6 kV conforming to IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	Trip indicator
Mounting Mode	Removable comb busbar installed
Mounting Support	DIN rail
9 Mm Pitches	2
Width	18 mm
Colour	White
Connections - Terminals	Single terminal (top or bottom) 1...25 mm² rigid Single terminal (top or bottom) 1...16 mm² flexible
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	2 N.m top or bottom
Earth-Leakage Protection	Without

Environment

Ip Degree Of Protection	IP20 B conforming to EN/IEC 60529
Pollution Degree	3 conforming to EN 60947-2 3 conforming to IEC 60947-2
Overvoltage Category	II
Tropicalisation	2 conforming to EN/IEC 60068-2-78
Relative Humidity	95 %
Operating Altitude	0...2000 m
Ambient Air Temperature For Operation	-35...70 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	1.8 cm
Package 1 Length	9.4 cm
Package 1 Weight	113.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.0 cm
Package 2 Width	9.8 cm
Package 2 Length	22.5 cm
Package 2 Weight	1.361 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	132

Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	15.458 kg

Contractual warranty

Warranty	18 months
----------	-----------