Product datasheet

Specification





Acti9 iC60H 4P 6A C Miniature Circuit breaker

Local distributor code: 396791227

A9F54406

EAN Code: 3606480515071

Main

| Range | Acti9 | |
|---------------------------|--|--|
| Product Name | Disbo iC60 | |
| Product Or Component Type | Miniature circuit-breaker | |
| Device Short Name | iC60H | |
| Poles Description | 4P | |
| Number Of Protected Poles | 4 | |
| [In] Rated Current | 6 A | |
| Network Type | AC/DC | |
| Trip Unit Technology | Thermal-magnetic | |
| Curve Code | С | |
| Breaking Capacity | 15 kA Icu at <= 250 V DC conforming to EN/IEC 60947-2 10000 A Icn at 415 V AC 50/60 Hz conforming to EN/IEC 60898-1 42 kA Icu at 12133 V AC 50/60 Hz conforming to EN/IEC 60947-2 30 kA Icu at 220240 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA Icu at 380415 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 | |
| Utilisation Category | Category A conforming to EN/IEC 60947-2 | |

Complementary

| Network Frequency | 50/60 Hz |
|--|---|
| Magnetic Tripping Limit | 8 x In +/- 20 % |
| [Ics] Rated Service Breaking Capacity | 21 kA 50 % conforming to EN/IEC 60947-2 - 12133 V AC 50/60 Hz 15 kA 50 % conforming to EN/IEC 60947-2 - 220240 V AC 50/60 Hz 7.5 kA 50 % conforming to EN/IEC 60947-2 - 380415 V AC 50/60 Hz 5 kA 50 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 7500 A 75 % conforming to EN/IEC 60898-1 - 415 V AC 50/60 Hz 10 kA 100 % conforming to EN/IEC 60947-2 - 100133 V DC |
| Limitation Class | 3 conforming to EN/IEC 60947-2 |
| [Ui] Rated Insulation Voltage | 500 V AC 50/60 Hz conforming to EN/IEC 60947-2 |
| [Uimp] Rated Impulse Withstand Voltage | 6 kV conforming to EN/IEC 60947-2 |
| Contact Position Indicator | Yes |
| Control Type | Toggle |
| Local Signalling | Trip indicator |
| Mounting Mode | Clip-on |
| Mounting Support | Rail |
| 9 Mm Pitches | 8 |

| Height | 85 mm | |
|--------------------------|--|--|
| Width | 72 mm | |
| Depth | 78.5 mm | |
| Net Weight | 0.5 kg | |
| Colour | White | |
| Mechanical Durability | 20000 cycles | |
| Electrical Durability | 10000 cycles | |
| Provision For Padlocking | Padlockable | |
| Connections - Terminals | Single terminal (top or bottom) 125 mm² rigid Single terminal (top or bottom) 116 mm² flexible | |
| Wire Stripping Length | 14 mm for top or bottom connection | |
| Tightening Torque | 2 N.m top or bottom | |
| Earth-Leakage Protection | Separate block | |

Environment

| Standards | EN/IEC 60947-2 EN/IEC 60898-1 |
|---------------------------------------|----------------------------------|
| Ip Degree Of Protection | IP20 conforming to IEC 60529 |
| Pollution Degree | 3 conforming to EN/IEC 60947-2 |
| Tropicalisation | 2 conforming to IEC 60068-1 |
| Relative Humidity | 95 % at 55 °C |
| Ambient Air Temperature For Operation | -3570 °C |
| Ambient Air Temperature For Storage | -4085 °C |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 7.2 cm |
| Package 1 Width | 7.5 cm |
| Package 1 Length | 9.0 cm |
| Package 1 Weight | 430.0 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 3 |
| Package 2 Height | 8.5 cm |
| Package 2 Width | 9.8 cm |
| Package 2 Length | 22.0 cm |
| Package 2 Weight | 1.337 kg |
| Unit Type Of Package 3 | S03 |
| Number Of Units In Package 3 | 33 |
| Package 3 Height | 30.0 cm |
| Package 3 Width | 30.0 cm |
| Package 3 Length | 40.0 cm |
| | |

Package 3 Weight

Contractual warranty

Warranty 18 months

15.326 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |