Product datasheet

Specification





sub-base - soldered solid state output relay ABE7 - 16 inputs - 48 V DC

Local distributor code: 402703675

ABE7S16E2E1

EAN Code: 3389110546255

Main

| Range Of Product | Modicon ABE7 | |
|--------------------------------|---|--|
| Product Or Component Type | Solid state input relay sub-base | |
| [Us] Rated Supply Voltage | 24 V DC (PLC end) 48 V DC (sensor end) | |
| Number Of Channels | 16 | |
| Number Of Terminal Per Channel | 2 | |
| Connections - Terminals | Screw type terminals, 1 x 0.091 x 1.5 mm², 0.091.5 mm² (AWG 28AWG 16) flexible with cable end Screw type terminals, 1 x 0.141 x 2.5 mm², 0.142.5 mm² (AWG 26AWG 12) | |
| | solid | |
| | Screw type terminals, 1 x 0.141 x 2.5 mm², 0.142.5 mm² (AWG 26AWG 14) flexible without cable end | |
| | Screw type terminals, 2 x 0.092 x 0.75 mm², 0.090.75 mm² (AWG 28AWG 20) flexible with cable end | |
| | Screw type terminals, 2 x 0.22 x 2.5 mm², 0.22.5 mm² (AWG 24AWG 14) solid | |

Complementary

| Terminal Block Type | Removable |
|--|--|
| Supply Voltage Limits | 1930 V DC (PLC end) conforming to IEC 61131-2 |
| Isolation Plc/Operative Part | Yes |
| Protection Type | Internal fuse 1 A 5 x 20 mm fast blow PLC end Adjustable by external fuse fast blow sensor end |
| Fixing Mode | By clips (35 mm symmetrical DIN rail) By screws (solid plate with fixing kit) |
| Current Per Channel | 0.013 A |
| Current State 1 Guaranteed | >= 6 mA (sensor end) |
| Voltage State 1 Guaranteed | >= 30 V for sensor end |
| Maximum Switching Current | 15 mA (PLC end) |
| Minimum Switching Current | 1 mA for PLC end |
| Response Time | <= 0.05 ms from state 0 to 1 <= 0.4 ms from state 1 to 0 |
| Switching Frequency | <= 1000 Hz duty cycle: 50 % |
| [Uimp] Rated Impulse Withstand Voltage | 2.5 kV conforming to IEC 60947-1 |
| [Ui] Rated Insulation Voltage | 2000 V |
| Installation Category | II conforming to IEC 60664-1 |
| Tightening Torque | 0.6 N.m with flat Ø 3.5 mm screwdriver |
| Net Weight | 0.37 kg |

Environment

| Dielectric Strength | 2000 V at 50/60 Hz conforming to IEC 60947-1 |
|---------------------------------------|--|
| Product Certifications | CSA UL DNV GL EAC |
| Standards | IEC 61131-2 Type 2 |
| Ip Degree Of Protection | IP2X conforming to IEC 60529 |
| Resistance To Incandescent Wire | 750 °C conforming to IEC 60695-2-11 |
| Shock Resistance | 15 gn for 11 ms conforming to IEC 60068-2-27 |
| Vibration Resistance | 2 gn (f= 10150 Hz) conforming to IEC 60068-2-6 |
| Resistance To Electrostatic Discharge | 4 kV (contact) level 3 conforming to IEC 61000-4-2 8 kV (air) level 3 conforming to IEC 61000-4-2 |
| Resistance To Radiated Fields | 10 V/m (260000001000000000 Hz) conforming to IEC 61000-4-3 level 3 |
| Resistance To Fast Transients | 2 kV level 3 conforming to IEC 61000-4-4 |
| Ambient Air Temperature For Operation | -560 °C conforming to IEC 61131-2 |
| Ambient Air Temperature For Storage | -4080 °C conforming to IEC 61131-2 |
| Pollution Degree | 2 conforming to IEC 60664-1 |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 7.0 cm |
| Package 1 Width | 8.3 cm |
| Package 1 Length | 21.1 cm |
| Package 1 Weight | 446.0 g |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 16 |
| Package 2 Height | 30.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 7.63 kg |

Logistical informations

Country Of Origin FR

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information


Yes

Certifications & Standards

| Reach Regulation | REACh Declaration | |
|--------------------------|---|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | |
| China Rohs Regulation | China RoHS declaration | |
| Environmental Disclosure | Product Environmental Profile | |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins | |
| Circularity Profile | End of Life Information | |

Dimensions Drawings

Dimensions




(1) ABE7BV20 / ABE7BV20E

ABE7S16E2E1

Mounting and Clearance


Mounting




ABE7S16E2E1

Connections and Schema

HE10 16 Channels



Wiring Diagram




| ABE7 | U1, U2 |
|-----------------|---------|
| S16E2B1 / E2B1E | 24 VDC |
| S16E2E1 / E2E1E | 48 VDC |
| S16E2E0 / E2E0E | 48 VAC |
| S16E2F0 / E2F0E | 115 VAC |
| S16E2M0 / E2M0E | 230 VAC |

Performance Curves

Curves for Determining Cable Type and Length According to the Current

16-channel Sub-base



- L Cable length
- I_{T} Total current per sub base (A)
- I_A Average current per channel (mA)
- (1) TSXCDP••2 and ABFH20H••0 cables with c.s.a. 0.08 mm² (AWG 28).
- (2) TSXCDP••3 cables with c.s.a. 0.34 mm² (AWG 22).
- (3) Cables with c.s.a. 0.13 mm² (AWG 26).

The curves are given for a voltage drop of 1 V in the cable. For n volts tolerance, multiply the length determined from the graph by n.