Product datasheet





sub-base - soldered solid state output relay ABE7 - 16 inputs -230 V AC

ABE7S16E2M0E

EAN Code: 3389110838831



Main

Range Of Product	Modicon ABE7	
Product Or Component Type	Solid state input relay sub-base	
[Us] Rated Supply Voltage	24 V DC (PLC end) 230/240 V AC 50/60 Hz (sensor end)	
Number Of Channels	16	
Number Of Terminal Per Channel	2	
Connections - Terminals	Spring terminal, 1 x 0.091 x 1.5 mm 2 (AWG 28AWG 16) flexible with cable end Spring terminal, 1 x 0.141 x 2.5 mm 2 (AWG 26AWG 12) solid Spring terminal, 1 x 0.141 x 2.5 mm 2 (AWG 26AWG 14) flexible without cable end	

Complementary

Terminal Block Type	Removable
Supply Voltage Limits	1930 V DC (PLC end) conforming to IEC 61131-2 264 V AC (sensor end) conforming to IEC 61131-2
Isolation Plc/Operative Part	Yes
Protection Type	Internal fuse 1 A 5 x 20 mm fast blow PLC end Adjustable by external fuse fast blow sensor end
Fixing Mode	By clips (35 mm symmetrical DIN rail) By screws (solid plate with fixing kit)
Current Per Channel	0.008 A
Current State 0 Guaranteed	<= 2 mA (sensor end)
Voltage State 0 Guaranteed	<= 40 V for sensor end
Current State 1 Guaranteed	>= 4.5 mA (sensor end)
Voltage State 1 Guaranteed	>= 164 V for sensor end
Maximum Switching Current	15 mA (PLC end)
Minimum Switching Current	1 mA for PLC end
Maximum Residual Current	0.1 mA at state 0 (PLC end)
Maximum Voltage Drop	<1 V at state 1 PLC end
Response Time	<= 20 ms from state 0 to 1 <= 20 ms from state 1 to 0
Switching Frequency	<= 25 Hz duty cycle: 50 %
[Uimp] Rated Impulse Withstand Voltage	2.5 kV conforming to IEC 60947-1
[Ui] Rated Insulation Voltage	2000 V

Life Is On Schneider 23 Apr 2024



Installation Category	II conforming to IEC 60664-1	
Tightening Torque	0.6 N.m with flat Ø 3.5 mm screwdriver	
Net Weight	0.407 kg	

Environment

Dielectric Strength	2000 V at 50/60 Hz conforming to IEC 60947-1	
Standards	IEC 61131-2 Type 1	
Ip Degree Of Protection	IP2X conforming to IEC 60529	
Resistance To Incandescent Wire	750 °C, extinction time <30 s conforming to IEC 60695-2-11	
Shock Resistance	15 gn for 11 ms conforming to IEC 60068-2-27	
Vibration Resistance	2 gn (f= 10150 Hz) conforming to IEC 60068-2-6	
Resistance To Electrostatic Discharge	4 kV (contact) level 3 conforming to IEC 61000-4-2 8 kV (air) level 3 conforming to IEC 61000-4-2	
Resistance To Radiated Fields	10 V/m (260000001000000000 Hz) conforming to IEC 61000-4-3 level 3	
Resistance To Fast Transients	2 kV level 3 conforming to IEC 61000-4-4	
Ambient Air Temperature For Operation	-560 °C conforming to IEC 61131-2	
Ambient Air Temperature For Storage	-4080 °C conforming to IEC 61131-2	
Pollution Degree	2 conforming to IEC 60664-1	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information


Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	

Dimensions Drawings

Dimensions




(1) ABE7BV20 / ABE7BV20E

ABE7S16E2M0E

Mounting and Clearance


Mounting




ABE7S16E2M0E

Connections and Schema

HE10 16 Channels



Wiring Diagram




ABE7	U1, U2
S16E2B1 / E2B1E	24 VDC
S16E2E1 / E2E1E	48 VDC
S16E2E0 / E2E0E	48 VAC
S16E2F0 / E2F0E	115 VAC
S16E2M0 / E2M0E	230 VAC

Performance Curves

Curves for Determining Cable Type and Length According to the Current

16-channel Sub-base



- L Cable length
- I_{T} Total current per sub base (A)
- I_A Average current per channel (mA)
- (1) TSXCDP••2 and ABFH20H••0 cables with c.s.a. 0.08 mm² (AWG 28).
- (2) TSXCDP••3 cables with c.s.a. 0.34 mm² (AWG 22).
- (3) Cables with c.s.a. 0.13 mm² (AWG 26).

The curves are given for a voltage drop of 1 V in the cable. For n volts tolerance, multiply the length determined from the graph by n.